## **MESSTEC Power Converter GmbH**

# Data Sheet Fast Modulator FM 40-50

0 ... 40 A

0 ... 80 A 0 ... 49 V

1960 W max

1 V ... 50 V 40 A max

3 V ... 6 V

10 MHz max

100 kHz max

50 ns

50 ns

TTL

TTL

Required

240 g 10100316

95 x 61 x 20 mm

60 W max allowed



#### Features

Drives arbitrary current waveforms into laser diodes CW, pulsed, modulated or mixed curves Very short rise and fall time Excellent dynamic performance Two analog inputs plus BIAS current Small dimensions, low weight

#### Specification

Diode current CW Diode current short pulses Diode voltage Output power Power dissipation Supply voltage Supply current Supply voltage\* Rise time Fall time Frequency (set point 1) Frequency (set point 2) Inputs Diode current set point 1 Diode current set point 2 Enable Reset

#### Outputs

Diode current monitor Temperature Ready Excess temperature

#### **General specifications**

Ambient temperature	
Cooling	
Dimensions	
Weight	
Ordering Code	
* for internal electronics	

TTL TTL -5°C ... +65 °C

0 ... 4 V for 0 ... 80°C

0 ... 500 mV (50 Ohm input)

0 ... 5 V (high impedance)

0 ... 50 mV (into 50 Ohm)





#### Description

The fast diode current modulator FM 40-50 is a linear modulator with improved properties for driving arbitrary current waveforms or fast pulses into laser diodes. Current waveforms can be CW, pulsed, modulated or mixed with frequencies up to 10 MHz and currents up to 40 A for CW and 80 A for pulsed waveforms. The modulator is small and compact and it is designed for mounting with low inductance directly at laser diodes or for integrating in laser diode modules. It has two analogue inputs for the current set point: high frequency input (50 Ohm input impedance) with a bandwidth of 10 MHz and a low frequency input with a bandwidth of 100 KHz. Additionally there is a 10 turns potentiometer for generating a CW-current (bias current). All set points are added and build the effective current set point. Technical subjects to change without notice.



### Warning! Risk of exposure of hazardous laser radiation in combination with laser light emitting devices!

Document: 10100316	Revision: 0	Date: 30.01.2015
www.powerconverter.eu	info@powerconverter.eu	+49 (0) 8856 803060